



75 A, Type QH Fuselinks, 23" Length, Removable Head

By Chance
Catalog # [M75QHA23](#)

75 amp, Type QH Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.

Features

- Comparable to Cooper/Kearney Type QA fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M75QHA23
Fuse Head Style	Removable
Fuselink Type	Type QH
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359631156

Dimensions



Length - Fuselink 23" (584.2mm)

Electrical Ratings

Amperage Rating 75 A

Logistics

Pallet Quantity 4800
Standard Package 10

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type QH](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type QH](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Type QH Fuse Links, Solid & Removable Head](#)
- [Specifications - M75QHA23](#)
- [Test Documents - QH Total Clear](#)
- [Test Documents - QH Min Melt](#)



A Hubbell brand