



7 A, Type MS Fuseinks, 26" Length, Removable Head

By Chance
Catalog # [M7MSA](#)

7 amp, Type MS Cutout fuselink with a 26" (660.4mm) pigtail and a removable buttonhead.


Features

- Comparable to Cooper/Kearney Type KS fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Dual element design
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

General

Catalog Number	M7MSA
Fuse Head Style	Removable
Fuselink Type	Type MS
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359049258

Dimensions



Length - Fuselink	26" (660.4mm)
Weight	0.098 lb

Electrical Ratings

Amperage Rating	7 A
-----------------	-----

Logistics

Pallet Quantity	4800
Standard Package	10

Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type MS](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type MS](#)
- [Literature - Switching Line Card_FAQ_2019](#)
- [Sales Drawings - Fuse Links, Type MSA Removable HD](#)
- [Specifications - M7MSA](#)
- [Test Documents - MS Min Melt](#)
- [Test Documents - MS Total Clear](#)



A Hubbell brand