



# 7 A, Type MS Fuseinks, 23" Length, Removable Head

By Chance  
Catalog # [M7MSA23](#)

7 amp, Type MS Cutout fuselink with a 23" (584.2mm) pigtail and a removable buttonhead.

## Features

- Comparable to Cooper/Kearney Type KS fuse links
- Compliant with ANSI/IEEE C37.42 - 2016 mechanical interchangeability requirements
- Compatible with universal style expulsion fuse holders
- Dual element design
- Individually packed for all weather protection
- Type and Current Rating on packaging and fuse for easy identification

## General

Catalog Number	M7MSA23
Fuse Head Style	Removable
Fuselink Type	Type MS
Required Cutout Fuse holder	100 Amp (Do not use in a 200 amp fuseholder.)
Type	Fuselinks
UPC	096359049265

## Dimensions

Length - Fuselink	23" (584.2mm)
Weight	0.088 lb



## Electrical Ratings

Amperage Rating	7 A
-----------------	-----

## Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

## Logistics

Pallet Quantity	4800
Standard Package	10

## Product Assets

- [Catalogs - Fuse Links](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Total Clearing Type MS](#)
- [Excel Files - Hubbell Time Current Characteristic Curve - Minimum Melt Type MS](#)
- [Literature - Switching Line Card\\_FAQ\\_2019](#)
- [Sales Drawings - Fuse Links, Type MSA Removable HD](#)
- [Specifications - M7MSA23](#)
- [Test Documents - MS Min Melt](#)
- [Test Documents - MS Total Clear](#)



A Hubbell brand