



LoadLocker Ammeter, Up to 500kV, 50 Hertz Unit

By CHANCE Utility
Catalog # [MEAMP32RN2](#)

U-shape jaw senses the amperage present between tines, narrow jaw for up to 5000 Amps



Features

- Open-end design lets you check loads on components not accessible by other hot-line ammeters
- Universal fitting mounts on insulated hotsticks
- Single button operation
- HOLD feature lets you bring down single reading to eye level
- Auto shut off after five minutes idle, or manually turn off by depressing button for five seconds

General

Duty N/A
UPC 096359570486

Dimensions

Jaw Width 2.50"
Weight 3.038 lb

Electrical Ratings

Amperage - Display Range 0-99.9 Amperes (0.1 Amp increments); 100-1999 Amperes (1.0 Amp increments); 2000-5000 Amperes (0.01 kA increments)

Amperage Rating Up to 5000 A
Withstand Voltage Up to 500 kV

Product Assets

[Catalogs - Instruments and Meters \(2450\)](#)
[Installation Manuals - CHANCE LoadLocker Ammeter Operator's Manual \(P400-2567\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-MEAMP32RN2-SPEC-EN | REV 7/2023