



T-SECTION UNDERGROUND CABLE RACK, 27-1/2in LENGTH

By Chance
Catalog # [PS1225](#)

Cable racking mounts to wall with expansion or anchor bolts for support of cable in underground vault applications. Support hooks (stanchions) and insulator pads complete the installation and are purchased seperately.

Features

- 1/4" X 2-1/4" X 2-1/4" steel T-section
- One 11/16" hole and one 11/16" open-ended slot on 26-1/2" centers for mounting
- 14 support hook holes
- Hot dip galvanized per ASTM A-153
- In compliance with ANSI C135.35 standard

General

Catalog Number	PS1225
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Number of Holes	14
UPC	096359068266

Dimensions



Dimensions	28.000 in x 3.000 in x 3.000 in
Distance From Pole	N/A
Height	3 in
Length	28 in
Weight	7.67 lb
Width	3 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	250
-----------------	-----

Product Assets

- [Catalogs - Pole Line Hardware](#)
- [Sales Drawings - Underground Cable Rack](#)
- [Specifications - PS1225](#)



A Hubbell brand