



# BOLT, OVALEYE, 3/4in x 26in

By Chance  
Catalog # [PS2050465CW](#)

Ovaleye bolts are used to support suspension insulators in deadend applications.



\*Representative Image

## Features

- 6" thread length and cone point
- Includes one square nut
- Rated tensile strength is 22,000 lbs.
- Manufactured in compliance with Canadian CSA C83-96 specification and Charpy level 1 impact properties with average minimum energy absorption of 20 joules when tested at -20 degrees C per ASTM A370
- Galvanized steel per CSAG164-M

## General

Catalog Number	PS2050465CW
Coating	Galvanized, CSA G164-M
Material	Steel
Tensile Strength	22000 lb.
UPC	096359628798

## Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	26 in
Length - Threaded Area	6 in
Weight	0 lb

## Certifications And Compliance

Industry Standard(s)	CSA C83.65
----------------------	------------

## Logistics

Carton Quantity	10
Pallet Quantity	490

## Product Assets

- [Catalogs - Fasteners - Canadian Standard \(CSA\)](#)
- [Sales Drawings - 5/8" & 3/4" Oval eye Bolt \(Cold Weather\)](#)
- [Specifications - PS2050465CW](#)