



# BOLT, OVALEYE, 5/8in x 14in

By Chance  
Catalog # [PS29964CW](#)



Ovaleye bolts are used to support suspension insulators in deadend applications.

## Features

- 6" thread length and cone point
- Includes one square nut
- Rated tensile strength is 14,100 lbs.
- Manufactured in compliance with Canadian CSA C83-96 specification and Charpy level 1 impact properties with average minimum energy absorption of 20 joules when tested at -20 degrees C per ASTM A370
- Galvanized steel per CSAG164-M

## General

|                  |                        |
|------------------|------------------------|
| Catalog Number   | PS29964CW              |
| Coating          | Galvanized, CSA G164-M |
| Material         | Steel                  |
| Tensile Strength | 14100 lb.              |
| UPC              | 096359573531           |

## Dimensions

|                        |         |
|------------------------|---------|
| Diameter               | 0.63 in |
| Diameter (Fraction)    | 5/8 in  |
| Distance From Pole     | N/A     |
| Length                 | 14 in   |
| Length - Threaded Area | 6 in    |
| Weight                 | 0 lb    |

## Certifications And Compliance

|                      |            |
|----------------------|------------|
| Industry Standard(s) | CSA C83.65 |
|----------------------|------------|

## Logistics

|                 |      |
|-----------------|------|
| Carton Quantity | 25   |
| Pallet Quantity | 1000 |

## Product Assets

[Catalogs - Fasteners - Canadian Standard \(CSA\)](#)  
[Sales Drawings - 5/8" & 3/4" Ovaleye Bolt \(Cold Weather\)](#)  
[Specifications - PS29964CW](#)



A Hubbell brand