



BOLT, OVALEYE, 3/4in x 20in

By Chance

Catalog # [PS29990CW](#)

Ovaleye bolts are used to support suspension insulators in deadend applications.



Features

- 6" thread length and cone point
- Includes one square nut
- Rated tensile strength is 22,000 lbs.
- Manufactured in compliance with Canadian CSA C83-96 specification and Charpy level 1 impact properties with average minimum energy absorption of 20 joules when tested at -20 degrees C per ASTM A370
- Galvanized steel per CSAG164-M

General

Coating	Galvanized, CSA G164-M
Material	Steel
Tensile Strength	22000 lb.

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	20 in
Length - Threaded Area	6 in
Weight	0 lb

Certifications And Compliance

Industry Standard(s)	CSA C83.65
----------------------	------------

Product Assets

[Catalogs - Fasteners - Canadian Standard \(CSA\)](#)

[Sales Drawings - 5/8" & 3/4" Ovaleye Bolt \(Cold Weather\)](#)