



## BOLT, THIMBLEYE, STRAIGHT, 5/8in x 12in

By Chance  
Catalog # [PS5512CW](#)



Used in deadend applications with loop-type attachments.

### Features

- 6" thread length
- Includes one square nut and cone pointed end
- Internal eye dimensions are 9/16" x 11/16"
- Rated tensile strength is 14,100 lbs.
- Galvanized per CSA G164-M
- Manufactured in compliance with Canadian CSA C83-96 specification and Charpy level 1 impact properties with average minimum energy absorption of 20 joules when tested at -20 degrees C per ASTM A370

### General

Coating	Galvanized, CSA G164-M
Material	Steel
Tensile Strength	14100 lb.
Type	Thimbleye Bolts

### Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Distance From Pole	N/A
Length	12 in
Length - Threaded Area	6 in

### Certifications And Compliance

Industry Standard(s)	CSA C83.63
----------------------	------------

### Product Assets

[Catalogs - Fasteners - Canadian Standard \(CSA\)](#)  
[Sales Drawings - 5/8" Thimbleye Bolts \(Cold Weather\)](#)