



# BOLT, THIMBLEYE, STRAIGHT, 3/4in x 8in

By Hubbell  
Catalog # [PS5608](#)



Used in deadend applications with loop-type attachments.

## Features

- 4" thread length and cone pointed end
- Includes one square nut
- Internal eye dimensions are 11/16" x 13/16"
- Rated tensile strength is 18,350 lbs.
- Hot dip galvanized per ASTM A-153
- RUS listed, ao - Bolt, strand eye, straight (thimble eye)

## General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb.
Type	Thimbleye Bolts
UPC	096359513834

## Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Length	8.00 in
Length - Threaded Area	4
Weight	1.7 lb

## Logistics

Carton Quantity 25

## Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)  
[Sales Drawings - 3/4" Thimbleye Bolt \(SA5608\)](#)  
[Technical Solutions - CH-PS5608-SPEC-EN](#)

## Related Products

[6823 - 3in SQUARE CURVED WASHER for 3/4in BOLT SIZE, 7/8in HOLE](#)  
[C2050187 - SPRING WASHER, REGULAR-DUTY DOUBLE-COIL, 3/4in SIZE](#)  
[3513 - MF TYPE CURVED LOCK NUT, 3/4in THREAD](#)  
[6814 - 2-1/4in SQUARE FLAT WASHER for 3/4in BOLT SIZE, 13/16in HOLE](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-PS5608-SPEC-EN | REV 1/2024