



# BOLT, THIMBLEYE, STRAIGHT, 3/4in x 10in

By Hubbell  
Catalog # [PS5610CW](#)



Used in deadend applications with loop-type attachments.

## Features

- 6" thread length
- Includes one square nut and cone pointed end
- Rated tensile strength is 22,000 lbs.
- Galvanized per CSA G164-M
- Manufactured in compliance with Canadian CSA C83-96 specification and Charpy level 1 impact properties with average minimum energy absorption of 20 joules when tested at -20 degrees C per ASTM A370

## General

Coating	Galvanized, CSA G164-M
Material	Steel
Tensile Strength	22000 lb.
Type	Thimbleye Bolts
UPC	096359573333

## Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Length	10.00 in
Length - Threaded Area	6.00 in

## Certifications and Compliance

Industry Standard(s)	CSA C83.63
----------------------	------------

## Logistics

Carton Quantity	15
-----------------	----

## Product Assets

[Catalogs - Fasteners - Canadian Standard \(CSA\)](#)  
[Sales Drawings - 3/4" Thimbleye Bolts \(Cold Weather \(SAPS5606CW\)\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-PS5610CW-SPEC-EN | REV 1/2024