



## BOLT, SPOOL, SINGLE-UPSET, 5/8in x 16in

By Chance  
Catalog # [PS7745](#)

Spool bolts are used to support a spool insulator in the horizontal position in secondary applications. Industry slang is Upset Bolt.



### Features

- 6" thread length and cone pointed end
- Overall length is 20-3/4"
- Includes one square nut with cotter key
- Rated cantilever load is 1,900 lbs.
- Hot dip galvanized per ASTM A-153
- Manufactured in compliance with ANSI C135.31
- RUS listed, q - Bolt, double upset

### General

Catalog Number	PS7745
Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.
Type	Spool Bolts
UPC	096359520382

### Dimensions

Diameter	0.63 in
Diameter (Fraction)	5/8 in
Dimensions	21.000 in x 1.750 in x 1.750 in
Distance From Pole	N/A
Height	1.75 in
Length	21 in
Weight	1.9 lb
Width	1.75 in

### Logistics

Carton Quantity	20
Pallet Quantity	800

### Product Assets

[Catalogs - Pole Line Hardware](#)  
[Sales Drawings - Upset Spool Bolts Single And Double](#)



A Hubbell brand