



DOUBLE-ARMING BOLT, 3/4in x 38in w/4 NUTS

By CHANCE Utility
Catalog # [PS889838](#)



Full thread double-arming bolt for utility pole double arm construction. Rated for 18,350 lbs. tensile strength. Includes four assembled square nuts and cone point. Industry slang is DA bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	18350 lb
UPC	096359479000

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	38.00 in
Weight	4.5 lb

Logistics

Pallet Quantity	250
-----------------	-----

Product Assets

- [Catalogs - Communications Catalog \(CA12042E\)](#)
- [Catalogs - Machine Bolts & DA Bolts \(5-53Supp24-28\)](#)
- [Sales Drawings - Double-Arming Bolt \(SA8882\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-PS889838-SPEC-EN | REV 4/2023