



CROSSARM INSULATOR PIN with 1in LEAD THREAD, 6in SHAFT LENGTH and 3/4in x 6-1/2in SHANK

By Chance
Catalog # [PS890](#)

Insulator pin used to support pin type insulator with 1" NEMA internal thread on crossarm. Refer to sales drawing link for included hardware.

Features

- Cantilever load rating is 1,400 lbs. based on ANSI/IEEE 10 degree deflection criterea
- Minimum thread length of shank is 3-1/4"
- Galvanized steel per ASTM A-153

General

| | |
|----------------|------------------------|
| Catalog Number | PS890 |
| Coating | Galvanized, ASTM A-153 |
| Material | Steel |
| Type | Pins |
| UPC | 096359075905 |

Dimensions

| | |
|--------------------|---------------------------------|
| Dimensions | 12.750 in x 2.500 in x 2.500 in |
| Distance From Pole | N/A |



| | |
|------------------------|----------|
| Height | 2.5 in |
| Length | 12.75 in |
| Length - Threaded Area | 3.25 |
| Weight | 2.61 lb |
| Width | 2.5 in |

Certifications And Compliance

| | |
|----------------------|--------------|
| Industry Standard(s) | ANSI C135.17 |
|----------------------|--------------|

Logistics

| | |
|-----------------|-----|
| Pallet Quantity | 720 |
|-----------------|-----|

Product Assets

[Catalogs - Pole Line Hardware](#)
[Sales Drawings - Low Voltage Forged Steel Pin](#)
[Specifications - PS890](#)



A Hubbell brand