



BOLT, MACHINE, SQ HEAD, 3/4in x 18in, 20,050lbs RATED TENSILE STRENGTH

By CHANCE Utility
Catalog # [PS8918CW](#)



Square head machine bolt for utility pole and crossarm construction. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per CSA G-164-M
- Manufactured in compliance with Canadian CSA C83-96 specification
- Charpy level 1 impact - Avg. min. energy absorption of 20J, when tested at -20° C per ASTM A370

General

Coating	Galvanized, CSA G164-M
Material	Steel
Tensile Strength	22000 lb.
Type	Machine Bolts
UPC	096359390008

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Length	18.00 in
Length - Threaded Area	6.00 in
Weight	2.16 lb

Certifications and Compliance

Industry Standard(s)	CSA C83. 23
----------------------	-------------

Logistics

Carton Quantity	15
Pallet Quantity	720

Product Assets

[Catalogs - Fasteners - Canadian Standard \(CSA\)](#)
[Sales Drawings - Bolts, Machine \(Cold Weather CSA\) \(SAPS8908CW\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-PS8918CW-SPEC-EN | REV 1/2024