



POLE EYE PLATE GUY ATTACHMENT, DOUBLE-EYE, 42,000lbs RATED STRENGTH @ 45 DEGREES, 15/16in CLEVIS PIN HOLE

By CHANCE Utility
Catalog # [PSC2030528](#)

Pole eye plate has two 15/16" dia. pin hole for double clevis attachments. Rated for 42,000 lbs. tensile strength at 45 or 36,000 lbs. at 90 degrees. Has upper and lower 15/16" dia. holes for mounting bolts. There are no cleats on back side, allowing for non-wood pole mounting.

Features

- Wide base for stabilization
- Cast ductile iron per ASTM A-536
- galvanized per ASTM A-153

General

UPC 096359573104



Dimensions

Distance From Pole N/A

Logistics

Carton Quantity 3
Pallet Quantity 144

Product Assets

[Catalogs - Cast Iron Pole Line Hardware \(05A\)](#)
[Sales Drawings - Pole-Eye Plate \(SA2030528\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-PSC2030528-SPEC-EN | REV 4/2023