



## Crossarm Link Stick - 1,500 lb. (680 kg) Working Load Limit

By: CHANCE Lineman Tools & Equipment  
Catalog # [PSC4004132](#)



The CHANCE® Crossarm Link Stick provides a 1,500 lb. working load limit. It hooks over a dead-end crossarm (up to 3.75 in x 4.75 in) on one end and provides a butt swivel on the other end that allows for connection with a hoist for the purpose of providing quick set-up for tension relief to a dead-end insulator or other component. No hassles connecting a sling.

### Features

- 1-1/4"-diameter Epoxiglas™ pole with 21-1/2" insulating length
- Plastisol-coated 3/4"-diameter steel hook
- Hook's 5" opening fits standard 3-3/4" x 4-3/4" crossarms
- Galvanized-steel swivel eye on pole end for easy alignment
- Lifting eye on hook fitting for positioning by a hot line tool
- Rated working load: 1,500 lb. and 3,500 lb.

### General

Color	Gray
Max Load Lbs.	1500 lb
Style	Crossarm Link Stick
Swivel Top?	Yes
UPC	096359575818
Working Load Limit	1,500 lb
Working Load Limit Metric	680 kg

### Dimensions

Dimensions	21.5 in x 5 in x 5 in
Height	5 in
Length	21.5 in
Length - Insulated Section	21.5 in
LengthMetric	546 mm
Weight	8 lb
WeightMetric	3.6 kg
Width	5 in

### Product Assets

[Catalogs - Mechanical Hoists \(1100\)](#)  
[Installation Manuals - CHANCE® Tools Manuals \(CENT\\_LTE\\_IOM\\_EN\\_00158\)](#)<LineBreak/>



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-PSC4004132-SPEC-EN | REV 4/2023