



15kV Load-Pickup Tool Set 12 ft (3.6 m) #2 Clear Jumper Handle

By Chance
Catalog # [PSC4031558CL](#)

12FT LOAD-PICK TO,OL SET #2 15KV CLEAR JUMPER HANDLE

Features

- Rated to pickup and carry up to 200 amp loads at 15kV
- Includes Load-Pickup Device, Clear Jumper Clamp, and 12ft of #2 15kV Jumper Cable
- Load-Pickup Tool and Jumper Clamp fit conductors from #6 Copper (0.162") through 795 ACSR (1.108")
- Clean and inspect Load-Pickup Tool head after every 25 operations or at least once every 90 days
- Adequate rubber gloves must be worn when using this equipment
- Orange-tinted translucent Lexan® housing permits easy visual inspection of the Load-Pickup head

General

Cable Length	12 ft
Cable Length Metric	3.6 m
Catalog Number	PSC4031558CL
UPC	096359826217

Dimensions



Cable Length Metric	3.6 m
Weight	19.6 lb
WeightMetric	8.8 kg

Electrical Ratings

Amperage Rating	200
Voltage - Maximum	15 kV

Conductor Related

Conductor Size	#2 AWG
----------------	--------

Logistics

Carton Quantity	1
Pallet Quantity	32

Product Assets

[Catalogs - Jumpers & Load Pickup Tools](#)
[Specifications - PSC4031558CL](#)



A Hubbell brand