



## Phasing Tester Kit, 10kV – 120kV

By CHANCE Utility  
Catalog # [PSC4033465](#)

Large, backlit, direct-reading display easily determines phase relationships and approximate voltage, line-to-line or line-to-ground on transmission circuits



### Features

- Kit Includes: (1) Instruction Manual, (1) PSC4033465 Tester (64" Long), (2) C4030459 Handles (96" Long), (1) P6218 Handle Bag, (1) C4030460 Bag for Tester
- Large Digital Display with Backlight and Hold modes
- Two high-impedance components in fiberglass poles, each threaded for interchangeable probes
- 22-foot-long insulated flexible cable from voltmeter stores on reel on other pole
- Must be used with 2 Epoxiglas Insulating Universal Hotsticks of appropriate length (included in kit)

### General

EU RoHS Indicator No  
UPC 096359470526

### Dimensions

Weight 39.0 lb

### Logistics

Standard Package 1

### Product Assets

[Catalogs - Instruments and Meters \(2450\)](#)  
[Installation Manuals - CHANCE Digital Transmission Phasing Testers Operating Instructions \(PSP4033468\)](#)

### Related Products

[H18766P - Pigtail Hook Probe](#)  
[H18765 - Angle Probe](#)  
[H18766S - Shepherd Hook Probe](#)  
[H18766 - Straight Probe](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-PSC4033465-SPEC-EN | REV 8/2023