



# CHANCE® Class 2, Temporary Conductor Cover, 6 ft.

By: CHANCE Lineman Tools & Equipment  
Catalog # [PSC4060617](#)



CHANCE® Class 2, Temporary Conductor Cover, 6 ft.

## Features

- Design tested to ASTM F712 Class 2
- Lightweight - Approximately 50% the weight of similar rubber hose
- Protects workers from accidental brush contact with energized components during line maintenance
- High visibility orange color
- Maximum use voltage of 14.6kV covered-phase-to-covered-phase
- 6 foot overall length

## General

Color - Jumper Insulation	Orange
Style	Rubber Glove Application
UPC	096359576280

## Dimensions

Weight	2.3 lb
--------	--------

## Electrical Ratings

Voltage Rating	Class 2 V
Withstand Voltage	15 kV Guarded Phase-to-Guarded Phase

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Catalogs - Cover-Up Equipment \(2400\)](#)  
[Literature - Cover-Up Care \(BR09003E\)](#)  
[Sales Drawings - Temporary Conductor Cover, Class 2 \(SA4060616\)](#)



A proud member of the Hubbell Family.