



Ground Clamp, C-Type, 5H

By CHANCE Utility
Catalog # PSC6003412

C-Type Grounding Clamp with eye screw, serrated jaw, 2" jaw opening, drilled ferrule hole, UNSHROUDED FERRULES ONLY, ASTM F855 Grade 5H



*Representative Image

Features

- Grade 5H Rated
- Rated 47kA with X/R = 30
- First cycle current peak = 127 kA
- Last cycle current peak = 70 kA
- Test duration = 15 cycles

General

EU RoHS Indicator	No
Eye Screw/T-Handle	250 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Handle Type	Eyescrew
Jaw Type	Serrated Jaws
Material	Aluminum
Terminal Connection Type	5/8"-11 Thread
UPC	096359453154

Dimensions

Jaw Opening Size - Maximum	2 in
Jaw Opening Size - Minimum	.162 in
Weight	1.75 lb

Electrical Ratings

Current Rating	400 A
Fault Current - 15 Cycles	47000 A
Grounding Wire Capacity Maximum	4/0 Cable w/ Threaded Terminal
Grounding Wire Capacity Minimum	#2 Cable w/ Threaded Terminal

Certifications and Compliance

Fault Current - ASTM Grade	5H
----------------------------	----

Logistics

Carton Quantity	15
Pallet Quantity	450

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)
[Sales Drawings - SA_6003412_](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-PSC6003412-SPEC-EN | REV 7/2023