



## Short Stud, 30mm, Female Threads, 5H

By CHANCE Utility  
Catalog # [PSC6003493](#)

5H Short Ball Stud, 30mm ball, .8" x .75" dia. shaft, 5/8-11 UNC Female Threads



### Features

- Grade 5H Rated
- Rated 47kA with X/R = 30
- First cycle current peak = 127 kA
- Last cycle current peak = 70 kA
- Test duration = 15 cycles

### General

UPC 096359567400

### Dimensions

Weight 1.6 lb

### Certifications and Compliance

Fault Current - ASTM Grade 5H

### Logistics

Carton Quantity 25  
Pallet Quantity 1125

### Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)  
[Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs \(CENT-LTE-H-RATED-GROUNDING-BR-EN-00301\\_web\)](#)  
[Sales Drawings - SA6003493](#)  
[Video - CHANCE Temporary Protective Grounding \(VI09071E0620\)](#)  
[Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-PSC6003493-SPEC-EN | REV 8/2023