



## CHANCE® Ground Clamp, C-Type, Type I-Class B-Grade 6H, 2.88in. Jaw Opening

By CHANCE Utility  
Catalog # [PSC6003700](#)

CHANCE® Ground Clamp, C-Type, Type I-Class B-Grade 6H, 2.88in. Jaw Opening



### Features

- C-Type Ground Clamp
- Continuous Current 400A
- Fault Current Rating 55kA, X/R=30
- Main Line Range Max. 2.88"
- Main Line Range Min. 0.625"
- Grounding Cable 4/0+
- ASTM Type I, Class B, Grade 6H
- Jaws Serrated
- Ferrule Threaded

### General

Eye Screw/T-Handle	300 in-lb
Installation Torque (in-lb)	
Ferrule Installation Torque (in-lb)	250 in-lb
Material	Aluminum
Maximum Bus Size	2.5 in
UPC	096359720805

### Dimensions

Weight 3.1 lb

### Logistics

Standard Package 1

### Product Assets

[Literature - New Chance® 6H Grounding C-Clamp \(SF09221E\)](#)  
[Sales Drawings - Serrated C Type Ground Clamp, 0.625"-2.8" \(SA6003700\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-PSC6003700-SPEC-EN | REV 8/2023