



Barry D.E.W. Line® Heavy Rope Link, 10 ft/3.0 m

By Chance
Catalog # [PSCDEWNK38X010](#)

Dielectric Even Wet insulating rope tool designed for performing live line work on AC or DC systems. One closed and one open spelter socket termination.

Features

- Rated Working Load 15,000 lb./6,803 kg
- Insulating Rope area is 1.25 in (32 mm) diameter
- Steel Spelter Socket Terminations retain 100% of rope’s breaking strength
- Available with two closed spelter socket terminations, two open spelter socket terminations, or one of each as pictured
- Available in custom lengths

General

Catalog Number	PSCDEWNK38X010
Working Load Limit	15,000 lb
Working Load Limit Metric	6,804 kg

Dimensions



*Representative Image

Diameter	1.25 in
Diameter - Metric	32 mm
Length	10 ft
Length Metric	3 m
Weight	42 lb
WeightMetric	19 kg

Product Assets

- [Brochures - Barry D.E.W. Line® Insulating Rope Tools](#)
- [Installation Manuals - Barry D.E.W. Line Insulating Rope Equipment](#)
- [Literature - CHANCE® Barry Insulating Rope Link](#)
- [Sales Drawings - SADEWNK38X010](#)
- [Specifications - PSCDEWNK38X010](#)



A Hubbell brand