



Barry D.E.W. Line® R1 Rescue Kit, 200 ft/60.9 m

By Chance
Catalog # [PSCDEWR1200](#)

Dielectric Even Wet self-contained, easily deployed system with retrievable anchor strap is designed to perform three different rescue methods and/or to escape from access platforms, buckets, and towers.



Features

- Rated Working Load 500 lb./226.7 kg
- Mode 1 - Self-rescue with retrievable anchor strap (allows user to self-retrieve rope and anchor strap after use)
- Mode 2 - Controlled descent of a victim from the position of the victim
- Mode 3 - Controlled descent of a victim from the ground (using a deviation pulley)
- System Includes: Barry D.E.W. Line® transport bag, Barry D.E.W. Line® Dielectric Tag Line with quick link, 1 Retrievable anchor strap, 200 ft/60.9 m Barry D.E.W. Line® Dielectric Rescue Rope, 1 Figure 8 rescue descender with ears, 2x 6 ft/1.8 m anchor straps, 1 forged ring, 1 Rescue pulley, 3 CSA carabiners, 1 Hotstick Rescue Clip Attachment

General

UPC	096359754275
Working Load Limit	500 lb
Working Load Limit Metric	226 kg

Dimensions

Length	200 ft
Length Metric	60.9 m
Weight	30.6 lb
WeightMetric	13.8 kg

Product Assets

[Installation Manuals - Barry D.E.W. Line Insulating Rope Equipment](#)
[Literature - CHANCE® Barry D.E.W. Line® Rethink Rope](#)