



Barry D.E.W. Line® Rescue Hoist Kit, 6 ft/1.8 m

By Chance

Catalog # [PSCDEWRH006](#)

Dielectric Even Wet self-contained, easily deployed lifting/hauling system designed to be used alone or in combination with Barry's Bucket Rescue Kit



Features

- Rated Working Load 500 lb./226.7 kg
- Mode 1 - Short distance lifting/hauling system for unhooking a victim from their fall protection equipment before lowering them to the ground
- Mode 2 - Stand-alone rescue hoist system for rescues at medium lift heights (max 50 ft/15.2 m reach)
- System Includes: 6 ft/1.8 m Barry D.E.W. Line® NF3400 Dielectric Rescue Rope, 1 Barry D.E.W. Line® transport bag, 1 Barry D.E.W. Line® Dielectric Tag Line, 2 Double Rescue Pulleys, 2 Steel Carabiner CSA, 1 6 ft/1.8 m Anchor Strap, 1 Hotstick Rescue Clip Attachment

General

| | |
|---------------------------|--------------|
| UPC | 096359757412 |
| Working Load Limit | 500 lb |
| Working Load Limit Metric | 226 kg |

Dimensions

| | |
|---------------|---------|
| Length | 6 ft |
| Length Metric | 1.8 m |
| Weight | 10.2 lb |
| WeightMetric | 4.6 kg |

Product Assets

[Installation Manuals - Barry D.E.W. Line Insulating Rope Equipment](#)

[Literature - CHANCE® Barry D.E.W. Line® Rethink Rope](#)



A Hubbell brand