



BOLT, DOUBLE END, 7/8in x 40in, w/2 NUTS

By Hubbell
Catalog # [PSDE784000](#)



Double end bolts are offered in a variety of lengths for support in double arm applications.

*Representative Image

Features

- 5" thread length on each end
- Includes two square nuts, one per end
- Rated tensile strength is 25,400 lbs.
- Galvanized per ASTM A-153
- Manufactured in compliance with ANSI C135.1

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	12400 lb.

Dimensions

Diameter	0.88 in
Diameter (Fraction)	7/8 in
Length	40.00 in
Length - Threaded Area	5

Product Assets

[Sales Drawings - 7/8" Double Ended Bolts \(SADE781200\)](#)
[Technical Solutions - CH-PSDE784000-SPEC-EN](#)

Related Products

[3514 - MF TYPE CURVED LOCK NUT, 7/8in THREAD](#)
[6819 - 4in SQUARE FLAT WASHER for 7/8in BOLT SIZE, 15/16in HOLE](#)
[PS6807 - WASHER, ROUND, 15/16in HOLE, 2-1/4in DIA.](#)
[680912 - 4in SQUARE CURVED WASHER for 7/8in BOLT SIZE, 15/16in HOLE](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-PSDE784000-SPEC-EN | REV 1/2024