



BOLT, MACHINE, SQ HEAD, 7/8in x 4in

By Chance
Catalog # PSSB780400



Square head machine bolt for utility pole and crossarm construction. Rated for 25,400 lbs. tensile strength. Includes one assembled square nut, cone point and 2" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1

General

Catalog Number	PSSB780400
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Tensile Strength	25400 lb.
Type	Machine Bolts
UPC	096359481898

Dimensions

Diameter	0.88 in
----------	---------

Diameter (Fraction)	7/8 in
Distance From Pole	N/A
Length	4 in
Length - Threaded Area	2
Weight	1.16 lb

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Logistics

Carton Quantity	30
Pallet Quantity	1920

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - 7/8 Machine Bolt Or Crossarm Bolt](#)