



BOLT, MACHINE, SQ HEAD, 7/8in x 5in

By Chance
Catalog # PSSB780500



Square head machine bolt for utility pole and crossarm construction. Rated for 25,400 lbs. tensile strength. Includes one assembled square nut, cone point and 2-1/2" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1

General

Catalog Number	PSSB780500
Coating	Galvanized, ASTM A-153
EU RoHS Indicator	No
Material	Steel
Tensile Strength	25400 lb.
Type	Machine Bolts
UPC	096359481904

Dimensions

Diameter	0.88 in
----------	---------

Diameter (Fraction)	7/8 in
Distance From Pole	N/A
Length	5 in
Length - Threaded Area	2.5

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Logistics

Carton Quantity	30
Pallet Quantity	1440

Product Assets

- [Catalogs - Communications Catalog](#)
- [Catalogs - Machine Bolts & DA Bolts](#)
- [Sales Drawings - 7/8 Machine Bolt Or Crossarm Bolt](#)