



BOLT, MACHINE, SQ HEAD, 7/8in x 26in

By CHANCE Utility
Catalog # [PSSB782600](#)



Square head machine bolt for utility pole and crossarm construction. Rated for 25,400 lbs. tensile strength. Includes one assembled square nut, cone point and 6" thread length. Common industry slang reference is crossarm bolt or through bolt.

Features

- Hot dip galvanized finish per ASTM A-153
- Manufactured in compliance with industry standard ANSI/IEEE C135.1
- RUS listed, c - Bolt, machine

General

Coating	Galvanized, ASTM A-153
Material	Steel
Tensile Strength	25400 lb
Type	Machine Bolts
UPC	096359479390

Dimensions

Diameter	0.88 in
Diameter (Fraction)	7/8 in
Distance From Pole	N/A
Length	26.00 in
Length - Threaded Area	8
Weight	4.3 lb

Certifications and Compliance

RUS Listed Reference c - Bolt, machine

Logistics

Carton Quantity 10
Pallet Quantity 400

Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)
[Catalogs - Machine Bolts & DA Bolts \(5-53Supp24-28\)](#)
[Sales Drawings - 7/8 Machine Bolt Or Crossarm Bolt \(SA2050254\)](#)

Related Products

[6819 - WASHER, SQ FLAT, 15/16in HOLE, 4in SQ](#)
[680912 - WASHER, SQ CURVED, 15/16in HOLE, 4in SQ](#)
[3514 - MF TYPE CURVED LOCK NUT, 7/8in THREAD](#)
[PS6807 - WASHER, ROUND, 15/16in HOLE, 2-1/4in DIA.](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-PSSB782600-SPEC-EN | REV 4/2023