



BOLT, SHOULDER EYE, 3/4in x 16in

By CHANCE Utility
Catalog # [PSSE3416CW](#)

Shoulder eye bolts are used to support suspension insulators in deadend applications. The flat base of the eye functions as a washer to protect structure of the wood member.



*Representative Image

Features

- 6" thread length
- Includes one square nut and cone pointed end
- Rated tensile strength is 22,000 lbs.
- Galvanized per CSA G164-M
- Manufactured in compliance with Canadian CSA C83-96 specification and Charpy level 1 impact properties with average minimum energy absorption of 20 joules when tested at -20 degrees C per ASTM A370

General

Coating	Galvanized, CSA G164-M
Material	Steel
Tensile Strength	22000 lb
UPC	096359573418

Dimensions

Diameter	0.75 in
Diameter (Fraction)	3/4 in
Distance From Pole	N/A
Length	16.00 in
Length - Threaded Area	6
Weight	0 lb

Certifications and Compliance

Industry Standard(s)	CSA C83.67
----------------------	------------

Logistics

Carton Quantity	15
Pallet Quantity	750

Product Assets

[Catalogs - Fasteners - Canadian Standard \(CSA\)](#)
[Sales Drawings - Shoulder Eye Bolts, 3/4 \(CW\) \(SAPSSE3406CW\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-PSSE3416CW-SPEC-EN | REV 4/2023