



CHANCE® Penetrating Cluster Bar, 1in. Dia by 11in. Long Bar, 36in. Chain, Grade 6H

By CHANCE Utility
Catalog # [PST6003466](#)



CHANCE® Penetrating Cluster Bar, 1in. Dia by 11in. Long Bar,
36in. Chain, Grade 6H

Features

- Used to create an Equi-Potential Zone (EPZ) on poles with temporary protective ground sets
- Designed and tested to ASTM F855 Grade 6H asymmetrical ultimate rating of 55kA at X/R=30
- 36in. of chain to wrap around pole
- 1in. diameter by 11in. long copper bar for mounting ground clamps

General

UPC 096359731719

Dimensions

Weight 12.0 lb

Certifications and Compliance

Fault Current - ASTM Grade 6H
Industry Standard(s) ASTM

Product Assets

[Catalogs - Grounding Equipment \(3000\)](#)
[Literature - ASTM H-Rated Grounding Sets, Clamps, and Ball Studs \(CENT-LTE-H-RATED-GROUNDING-BR-EN-00301_web\)](#)
[Literature - 5H 6H ClusterBars \(SF09124E\)](#)
[Video - CHANCE Temporary Protective Grounding \(VI09071E0620\)](#)
[Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-PST6003466-SPEC-EN | REV 8/2023