



CHANCE® Short Circuit Stick with 4 Clamps for Bare Vertical Secondary Overhead Systems (20cm spacing)

By CHANCE Utility
Catalog # [PST6003583](#)

CHANCE® Short Circuit Stick with 4 Clamps for Bare Vertical Secondary Overhead Systems (20cm spacing)



*Representative Image

Features

- Short Circuit Stick with spring loaded clamps for bare vertical secondary overhead systems
- Fault current rated and tested per IEC 61230 at 3kA/1 second
- Handle meets ASTM F711 and IEC 60855
- Clamps are spring loaded and allow connection of the phases to the neutral in one swift movement
- Conductor range: Min. 3.5mm up to Max. 19.5mm diameter
- Includes 4 clamps with 20cm vertical spacing

General

UPC 096359744351

Dimensions

Weight 1.2 kg

Logistics

Standard Package 1

Product Assets

- [Catalogs - Grounding Equipment \(3000\)](#)
- [Literature - SF_09_103S - ShortCircuit Stick 2019 \(Spanish\)](#)
- [Literature - SF_09_103E - ShortCircuit Stick 2019](#)
- [Sales Drawings - Short Circuit Stick with 4 clamps - 20 cm spacing](#)
- [Video - CHANCE Temporary Protective Grounding \(VI09072SP0720\)](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-PST6003583-SPEC-EN | REV 8/2023