



Anchor, Rock 2.25in X 30in 1in Rod

By Chance
Catalog # [R130LH](#)

Expanding Socket Rock Anchor 1" (25.4 mm) Diameter Rod, 30" (762 mm) long with Tripleye.



Features

- Anchor expands socket against solid walls of rock
- The large drop-forged Tripleye® rod holds up to three guy strands
- Requires 2.5" diameter hole in competent rock a minimum depth of 12"
- Hot dipped galvanized per ASTM A153

Application

Earth Tension Anchoring

General

Catalog Number	R130LH
Coating	Galvanized
Eyenuit Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5° of alignment with the guy load may significantly lower strength. Recommended minimum installation depth is 12" in solid rock.

Tensile Strength	36000 lb.
Type	Rock Anchors
UPC	096359809524

Dimensions

Anchor Hole Size	2.5 in
Diameter	2.25 in
Length	30 in
Rod Diameter	1 in

Logistics

Pallet Quantity	210 EA
Standard Package	3

Product Assets

- [Catalogs - Dependable Anchoring Solutions](#)
- [Catalogs - Anchors](#)
- [Catalogs - Communications Catalog](#)
- [Installation Manuals - Expanding Rock Anchor](#)
- [Installation Manuals - Expanding Rock Anchors - Socket Style](#)
- [Literature - Socket Style Rock Anchor](#)
- [Sales Drawings - SAR130LH](#)
- [Specifications - R130LH](#)



A Hubbell brand