



Anchor, Rock 2.25in X 53in 1in Rod

By Chance
Catalog # [R153L](#)

Expanding Rock Anchor 1" (25.4 mm) Diameter Rod, 53" (1346 mm) long with Tripleye.



Features

- Anchor expands and wedges against solid walls of rock
- The large drop-forged Tripleye® rod holds up to three guy strands
- Requires 2.5" diameter hole in competent rock a minimum depth of 12"
- Hot dipped galvanized per ASTM A153

Application

Earth Tension Anchoring

General

Catalog Number	R153L
Coating	Galvanized, ASTM A-153
Eyenuit Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5° of alignment with the guy load may significantly lower strength. Recommended minimum installation depth is 12" in solid rock.
Tensile Strength	36000 lb.
Type	Rock Anchors
UPC	096359051114

Dimensions

Anchor Hole Size	2.5 in
Diameter	2.25 in
Dimensions	53.000 in x 3.000 in x 3.000 in
Height	3 in
Length	53 in
Rod Diameter	1 in
Weight	17.963 lb
Width	3 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
--------------------------	---

Logistics

Pallet Quantity	51
Standard Package	3

Product Assets

- [Catalogs - Dependable Anchoring Solutions](#)
- [Catalogs - Anchors](#)
- [Catalogs - Communications Catalog](#)
- [Installation Manuals - Rock Anchor Wedge Style](#)
- [Sales Drawings - Expanding Rock Anchors 1" Rod](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - R153L](#)



A Hubbell brand