



## Anchor, Rock 1.75in X 53in 3/4in Rod

By Chance  
Catalog # [R353H](#)

Expanding Socket Rock Anchor 0.75" (19.1 mm) Diameter Rod, 53" (1346 mm) long with Tripleye.



### Features

- Anchor expands socket against solid walls of rock
- The large drop-forged Tripleye® rod holds up to three guy strands
- Requires 2" diameter hole in competent rock a minimum depth of 12"
- Hot dipped galvanized per ASTM A153

### General

Application	Earth Tension Anchoring
Coating	Galvanized
Eyenuit Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5° of alignment with the guy load may significantly lower strength. Recommended minimum installation depth is 12" in solid rock.
Tensile Strength	23000 lb.
Type	Rock Anchors

### Dimensions

Anchor Hole Size	2 in
Diameter	1.75 in
Length	53 in
Rod Diameter	0.75 in

### Logistics

Pallet Quantity	50 EA
Standard Package	5

### Product Assets

[Installation Manuals - Expanding Rock Anchor](#)  
[Installation Manuals - Expanding Rock Anchors - Socket Style](#)  
[Literature - Socket Style Rock Anchor](#)  
[Sales Drawings - SAR130LH](#)



A Hubbell brand