



## Anchor, Rock 1.75in X 60in 3/4in Rod

By CHANCE Utility  
Catalog # [R360](#)

Expanding Rock Anchor 0.75" (19.1 mm) Diameter Rod, 60" (1524 mm) long with Tripleye.



### Features

- Anchor expands and wedges against solid walls of rock
- The large drop-forged Tripleye® rod holds up to three guy strands
- Requires 2" diameter hole in competent rock a minimum depth of 12"
- Hot dipped galvanized per ASTM A153

### Application

Earth Tension Anchoring

### General

Coating	Galvanized, ASTM A-153
Eyenuit Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5° of alignment with the guy load may significantly lower strength. Recommended minimum installation depth is 12" in solid rock.
Tensile Strength	23000 lb.
Type	Rock Anchors
UPC	096359051176

### Dimensions

Anchor Hole Size	2 in
Diameter	1.75 in
Length	60.000 in
Rod Diameter	0.750 in
Weight	10.192 lb

### Logistics

Pallet Quantity	50
Standard Package	5

### Product Assets

[Catalogs - Anchors \(4\)](#)  
[Installation Manuals - Rock Anchor Wedge Style \(TD06162E\)](#)  
[Literature - Anchoring \(CA12002E\)](#)  
[Sales Drawings - Expanding Rock Anchors 3/4" Rod \(SAR315\)](#)  
[SDS - MSDS - Galvanized Steel Products](#)

### Related Products

[G5063 - Tripleye® ANCHOR ROD BONDING CLAMP for 3/4in & 1in EXPANDING, CROSSPLATE NO-WRENCH & ROCK ANCHORS](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
CH-R360-SPEC-EN | REV 4/2023