



Anchor, Rock 1.75in X 72in 3/4in Rod

By CHANCE Utility
Catalog # [R372](#)

Expanding Rock Anchor 0.75" (19.1 mm) Diameter Rod, 72" (1829 mm) long with Tripleye.



Features

- Anchor expands and wedges against solid walls of rock
- The large drop-forged Tripleye® rod holds up to three guy strands
- Requires 2" diameter hole in competent rock a minimum depth of 12"
- Hot dipped galvanized per ASTM A153

Application

Earth Tension Anchoring

General

Coating	Galvanized, ASTM A-153
Eyenuit Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5° of alignment with the guy load may significantly lower strength. Recommended minimum installation depth is 12" in solid rock.
Tensile Strength	23000 lb.
Type	Rock Anchors
UPC	096359051183

Dimensions

Anchor Hole Size	2 in
Diameter	1.75 in
Length	72.000 in
Rod Diameter	0.750 in
Weight	11.760 lb

Logistics

Pallet Quantity	48
Standard Package	4

Product Assets

[Catalogs - Anchors \(4\)](#)
[Installation Manuals - Rock Anchor Wedge Style \(TD06162E\)](#)
[Literature - Anchoring \(CA12002E\)](#)
[Sales Drawings - Expanding Rock Anchors 3/4" Rod \(SAR315\)](#)
[SDS - MSDS - Galvanized Steel Products](#)

Related Products

[G5063 - Tripleye® ANCHOR ROD BONDING CLAMP for 3/4in & 1in EXPANDING, CROSSPLATE NO-WRENCH & ROCK ANCHORS](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-R372-SPEC-EN | REV 4/2023