



Anchor, Rock 1.75in X 84in 3/4in Rod

By CHANCE Utility
Catalog # [R384H](#)

Expanding Socket Rock Anchor 0.75" (19.1 mm) Diameter Rod, 84" (2134 mm) long with Tripleye.



Features

- Anchor expands socket against solid walls of rock
- The large drop-forged Tripleye® rod holds up to three guy strands
- Requires 2" diameter hole in competent rock a minimum depth of 12"
- Hot dipped galvanized per ASTM A153

Application

Earth Tension Anchoring

General

Coating	Galvanized
Eyenuit Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5° of alignment with the guy load may significantly lower strength. Recommended minimum installation depth is 12" in solid rock.
Tensile Strength	23000 lb.
Type	Rock Anchors

Dimensions

Anchor Hole Size	2 in
Diameter	1.75 in
Length	84.000 in
Rod Diameter	0.750 in

Logistics

Pallet Quantity	48 EA
Standard Package	4

Product Assets

- [Installation Manuals - Expanding Rock Anchors - Socket Style \(TD06164E\)](#)
- [Installation Manuals - Expanding Rock Anchor \(TD06065E\)](#)
- [Literature - Socket Style Rock Anchor \(SF06163\)](#)
- [Sales Drawings - SAR130LH](#)

Related Products

[G5063 - Tripleye® ANCHOR ROD BONDING CLAMP for 3/4in & 1in EXPANDING, CROSSPLATE NO-WRENCH & ROCK ANCHORS](#)



A proud member of the Hubbell Family.