



Anchor, Rock 1.75in X 96in 3/4in Rod

By Chance
Catalog # [R396H](#)

Expanding Socket Rock Anchor 0.75" (19.1 mm) Diameter Rod, 96" (2438 mm) long with Tripleye.



Features

- Anchor expands socket against solid walls of rock
- The large drop-forged Tripleye® rod holds up to three guy strands
- Requires 2" diameter hole in competent rock a minimum depth of 12"
- Hot dipped galvanized per ASTM A153

General

Application	Earth Tension Anchoring
Coating	Galvanized
Eyenuit Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5° of alignment with the guy load may significantly lower strength. Recommended minimum installation depth is 12" in solid rock.
Tensile Strength	23000 lb.
Type	Rock Anchors

Dimensions

Anchor Hole Size	2 in
Diameter	1.75 in
Length	96 in
Rod Diameter	0.75 in

Logistics

Pallet Quantity	51 EA
Standard Package	3

Product Assets

- [Installation Manuals - Expanding Rock Anchor](#)
- [Installation Manuals - Expanding Rock Anchors - Socket Style](#)
- [Literature - Socket Style Rock Anchor](#)
- [Sales Drawings - SAR130LH](#)



A Hubbell brand