



Vertical Line Post Insulator Bracket, 10"

By CHANCE Utility
Catalog # [RPH10PF](#)

10" Heavy Duty Fiberglass Vertical Line Post Insulator Standoff Bracket



General

Description - End Fitting	Post Insulator
Strength Rating - Minimum Ultimate, Longitudinal (L)	2000 lb
Strength Rating - Minimum Ultimate, Transverse (T)	2000 lb
Strength Rating - Minimum Ultimate, Vertical (V)	5000 lb
UPC	096359610786

Dimensions

Diameter - Rod / Tube	2 in
Distance From Pole	10 in
Length	10.00 in
Mounting Bolt Spacing	<ul style="list-style-type: none">• 5.00 in• 6.00 in• 8.00 in
Weight	10.3 lb

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalog Page - CHANCE® Fiberglass Construction Products \(Page 12-23\)](#)
[Sales Drawings - Standoff, Vertical Post Insulator \(SA_RPHxxPF\)](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
CH-RPH10PF-SPEC-EN | REV 1/2024