



**Anchor, Tough One, 8in, 10,000 ft-lb rating, 2.25in hub, 1in threads, bevel leading edge**

By Chance  
Catalog # [T1022021](#)

Tough One Anchor Helix, 10,000 Ft Lbs (13,558 N-M), 8" (203 mm) beveled leading edge helix for use with 0.75" (19.1 mm) or 1" (25.4 mm) Rod.

**Features**

- Installed with Chance anchor wrench C1021583
- The anchor's sloped lead point improves penetration and helps soil flow from below the hub to above the anchor.
- 1" threads to fit 3/4" and 1" diameter Pisa rod
- Anchors are painted with a black paint

**Application**

Helical Anchoring

**General**

Catalog Number	T1022021
Coating	Painted
Number of Helices	1
Torque Rating	10000 ft-lbs
Type	Anchor Helix
UPC	096359054818

**Dimensions**

Anchor Helix Diameter(s)	8 in
Anchor Hub Size	2.25 in
Rod Diameter	<ul style="list-style-type: none"><li>• 0.75</li><li>• 1 in</li></ul>
Weight	10.261 lb

**Certifications And Compliance**

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

**Logistics**

Pallet Quantity	192
Standard Package	4

**Product Assets**

- [Catalogs - Anchor Tools](#)
- [Catalogs - Anchors](#)
- [Catalogs - Dependable Anchoring Solutions](#)
- [Installation Manuals - TOUGH ONE® Anchors](#)
- [Installation Manuals - Holding Capacity Chart - PISA Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - CHANCE Anchor Installation Tools: Product Feature & Selection Guide](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - How to Match Anchors and Installing Wrenches](#)
- [Literature - Power Installed Screw Anchor Offering](#)
- [Sales Drawings - Tough One 2-1/4 10,000](#)
- [Specifications - T1022021](#)
- [Video - CHANCE Pisa Drive Tools](#)
- [Video - CHANCE Tough One and PISA Anchor Installation](#)