



## Anchor, PISA Rod, Extension, 5/8in X 18in , 5/8in threads

By CHANCE Utility  
Catalog # [T1022320](#)

Pisa Rod Extension 0.625" (15.9 mm) diameter, 18" (457 mm) long.



### Features

- These anchor rod extensions primarily are for making above grade connections between installed anchors and guy wires.
- Hot dipped galvanized per ASTM A153
- Hot forged hex collar provides strong connection to anchor and eye

### Application

Helical Anchoring

### General

Coating	Galvanized, ASTM A-153
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	16000 lb.
Type	Power Installed Screw Anchor (PISA)
UPC	096359487081

### Dimensions

Length	18.000 in
Rod Diameter	0.625 in
Weight	1.52 lb

### Logistics

Carton Quantity	25
Pallet Quantity	1200
Standard Package	25

### Product Assets

[Installation Manuals - TD06131E\\_PISA\\_Anchors](#)  
[Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)  
[Sales Drawings - Anchor Rod, Power Screw \(SA1022320\)](#)  
[Video - CHANCE Tough One and PISA Anchor Installation \(VI0645E\)](#)  
[Video - CHANCE Pisa Drive Tools \(VI0633E\)](#)

### Related Products

[12589 - Anchor, PISA Nut, 5/8in threads, Twineye](#)  
[12587 - Anchor, PISA Nut, 5/8in threads, Thimbleye](#)  
[12593 - Anchor, PISA Nut, 5/8in threads, Tripleye](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
CH-T1022320-SPEC-EN | REV 1/2024