



Anchor, Adapter, SS175 Tripleye

By Chance
Catalog # [T1100465](#)

SS 175 Guy Adapter with Tripleye.



Features

- Guy adapters include a high-strength bolt and nut.
- Forged fittings on both ends of adapters
- Forged integral Pulling Eye speeds up guy installation
- Hot dipped galvanized per ASTM A153

Application

Helical Anchoring

General

Catalog Number	T1100465
Coating	Galvanized, ASTM A-153
Eyenut Style	Tripleye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength. Note: Pulling Eye Rated: 12,000 lbs. Guy wire should not be attached to pulling eye.
Tensile Strength	100000 lb.
Type	Adapters
UPC	096359055617

Dimensions

Dimensions	18.000 in x 5.500 in x 2.400 in
Height	2.4 in
Length	18 in
Weight	10.78 lb
Width	5.5 in

Logistics

Pallet Quantity	160
Standard Package	1

Product Assets

- [Catalogs - Anchors](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Installation Manuals - Holding Capacity Chart - SS175 Anchors](#)
- [Installation Manuals - Holding Capacity Chart - Soil Classification](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance](#)
- [Literature - Forged Pulling Eye](#)
- [Literature - Anchoring](#)
- [Sales Drawings - SS175 Anchors](#)
- [Sales Drawings - Forged Guy Adapter](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Specifications - T1100465](#)
- [Video - CHANCE Square Shaft Anchor Installation](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process](#)