



Anchor, Adapter, SS200 Tripleye

By CHANCE Utility
Catalog # [T1100629](#)

SS 200 Guy Adapter with Tripleye.



Features

- Guy adapters include a high-strength bolt and nut.
- Forged fittings on both ends of adapters
- Forged integral Pulling Eye speeds up guy installation
- Hot dipped galvanized per ASTM A153

Application

Helical Anchoring

General

| | |
|-------------------|---|
| Coating | Galvanized |
| EU RoHS Indicator | No |
| Eyenuit Style | Tripleye |
| Strength Note | Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength. Note: Pulling Eye Rated: 12,000 lbs. Guy wire should not be attached to pulling eye. |
| Tensile Strength | 100000 lb. |
| Type | Adapters |
| UPC | 096359055761 |

Dimensions

| | |
|------------|--------------------------------|
| Dimensions | 18.00 in x 6.625 in x 2.375 in |
| Height | 2.375 in |
| Length | 18.00 in |
| Weight | 11.750 lb |
| Width | 6.625 in |

Logistics

| | |
|------------------|-----|
| Pallet Quantity | 140 |
| Standard Package | 1 |

Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Forged Pulling Eye \(SF06013E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Forged Guy Adapter \(SA1020024\)](#)
- [SDS - MSDS - Galvanized Steel Products](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

[PSC2030521 - Tripleye® ANCHOR ROD BONDING CLAMP for SS & RR ANCHOR ADAPTERS and NO-WRENCH ANCHOR EXTENSION](#)



A proud member of the Hubbell Family.