



Anchor, Adapter, SS200 Twineye

By CHANCE Utility
Catalog # [T1101229](#)

SS 200 Guy Adapter with Twineye



*Representative Image

Features

- Guy adapters include a high-strength bolt and nut.
- Forged fittings on both ends of adapters
- Forged integral Pulling Eye speeds up guy installation
- Hot dipped galvanized per ASTM A153

Application

Helical Anchoring

General

Coating	Galvanized, ASTM A-153
Eyenuit Style	Twineye
Strength Note	Ultimate strength ratings apply to properly installed anchors only. Failure to install within 5 ° of alignment with the guy load may significantly lower strength.
Tensile Strength	100000 lb.
Type	Adapters
UPC	096359708667

Dimensions

Length	18.000 in
Weight	45 lb

Logistics

Standard Package 1

Product Assets

- [Catalogs - Anchors \(4\)](#)
- [Installation Manuals - TD06132E_Type_SS_and_RR_Anchors](#)
- [Literature - CHANCE Anchor Tool Inspection and Maintenance \(TD06031E\)](#)
- [Literature - Forged Pulling Eye \(SF06013E\)](#)
- [Literature - Anchoring \(CA12002E\)](#)
- [Sales Drawings - Forged Guy Adapter \(SA1020024\)](#)
- [Video - CHANCE Square Shaft Anchor Tools Selection Process \(VI0651E\)](#)
- [Video - CHANCE Square Shaft Anchor Installation \(VI0655E\)](#)

Related Products

[PSC2030520 - Twineye® ANCHOR BONDING CLAMP for SS & RR ANCHOR ADAPTERS and NO-WRENCH ANCHOR EXTENSION](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
CH-T1101229-SPEC-EN | REV 4/2023