



Pole Base Foundation , 4" OD x 84" Long

By CHANCE Utility
Catalog # T1120693

Decorative Streetlight Foundation (SLF) , 4" OD x 84" Long, 3/4" thick x 13" square baseplate, variable circle, hardware not included.



*Representative Image

Features

- Variable 6" - 14" Bolt Circle
- 4 slots, 3/4" Dia x 3-1/2" Long
- Suitable for Streetlight, Roadway, and Architectural Lighting
- Other applications include EV Charging Infrastructure, 5G/6G Poles, Rail Applications, End Zone Tower Systems, Solar Array Pole Mount, and Signage
- use Hardware Package T1120393

Application

Helical Anchoring

General

Base Plate Shape	Square
Bolt Hole Type	Slotted
Coating	Galvanized
EU RoHS Indicator	No
Ground Lug Hole	Yes
Number of Bolt Slots	4
Pipe Type	Round Pipe
Type	Lighting Foundation Anchors
UPC	096359363040
With Hardware	T1120393

Dimensions

Base Plate Dimensions	13.00 in
Base Plate Thickness	0.750 in
Bolt Length	3.50 in
Cableway Distance From Base	48 in
Cableway Length	3.00 in
Cableway Width	1.50 in
Center hole dimensions	3.60 in
Diameter - Bolt	0.75 in
Diameter - Bolt Circle	• 6 in • 14 in
Foundation Diameter	4.000 in
Foundation Length	84 in
Length	84.00 in
Weight	175.000 lb

Logistics

Pallet Quantity	20
Standard Package	1

Product Assets

- [Case Studies - Case History - Randazzo Park \(CH04318E_1120\)](#)
- [Installation Manuals - Instant Foundations \(TD04365E\)](#)
- [Literature - Instant Foundation Solutions \(SF04248E_0819\)](#)
- [Literature - Precast Concrete Collars \(SF04273E\)](#)
- [Literature - Instant Foundations® for EV Charging Stations \(SF04048E\)](#)
- [Literature - Instant Foundations and Pre-Cast Concrete Collars \(BR04331E\)](#)
- [Sales Drawings - Lighting Foundation \(SA112-0693\)](#)
- [Test Documents - Pole Load Determination Data Sheet \(TD04196E\)](#)
- [Video - CHANCE Instant Foundation & Concrete Collar \(VI04163E0520\)](#)
- [Video - SLF \(VI04173E1021\)](#)
- [Video - CHANCE® Instant Foundation System \(VI04150E_14L\)](#)



A proud member of the Hubbell Family.