CHANCE®

Double and Triple Blocks with 150 ft of 1/2 in Samson DURA-PLEX Rope

By CHANCE Utility
Catalog # T4001258

Rope is pre-installed for immediate use out of the box

Features

- Shells and sheaves are made of high dielectric, fiberfilled natural nylon
- Silicon Bronze Shaft with Oil-Impregnated Bronze Sheave Bearings
- Dielectric rating in dry weather is 30,000 volts between bearing and mounting bolt nut
- Maximum rope diameter accepted is 1/2"

General

Material	Composite Fiber Braided Rope
Max Load Lbs.	3500 lb
Style	Double & Triple Blocks w/ 150' of Rope
Swivel Top?	Yes
Type	Load Lift Assist
UPC	096359058526

Dimensions

Weight	4.41 lb
WeightMetric	2.00 kg

Logistics

Pallet Quantity	32

Product Assets

Catalogs - Load Handling Accessories (1250)

©2023 Hubbell Incorporated. All rights reserved.
CH-T4001258-SPEC-EN | REV 7/2023