



Dual Range Phasing Tester Kit, 1 & 16kV

By CHANCE Utility
Catalog # T4030786

DUAL RANGE Phasing Testers easily determine phase relationships and approximate voltage, line-to-line or line-to-ground



*Representative Image

Features

- Kit Includes: (1) Phasing Meter, (2) H17601 Six Foot Handles, (1) P6436 Handle Bag, (1) Tester, (2) Hook Probes, (1) Case, (1) Instruction manual
- For convenience on different systems, toggle can switch calibration between two scales on meter face
- Switching to Lo range improves readability for low-end values on Hi scale by increasing needle deflection for more finite readings
- 22-foot-long insulated flexible cable from voltmeter stores on reel on other pole
- Must be used with 2 Epoxiglas Insulating Universal Hotsticks of appropriate length (included in kit)

General

EU RoHS Indicator	No
Style	Analog Dial
UPC	096359059325

Dimensions

Weight	27.5 lb
--------	---------

Electrical Ratings

Withstand Voltage	1kV & 16kV
-------------------	------------

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Instruments and Meters \(2450\)](#)
- [Installation Manuals - CHANCE Phasing Testers Care and Operation Manual \(PSP4033469\)](#)
- [Video - CHANCE Meters and Instruments \(VI0955E\)](#)

Related Products

- [H18766P - Pigtail Hook Probe](#)
- [H18764 - Pair of Extension Resistors, Up to 48kV](#)
- [H18766S - Shepherd Hook Probe](#)
- [H18765 - Angle Probe](#)
- [H18766 - Straight Probe](#)



A proud member of the Hubbell Family.