



Telescoping Disconnect Stick 40 ft (12.1 m) Maximum Length

By CHANCE Lineman Grade Tools
Catalog # [T4033349](#)

Telescoping Disconnect Stick, 22 - 28 - 34 - 40'



Features

- Tested per OSHA & ASTM F711
- Allow linemen to perform many routine jobs from ground level
- Universal end fitting on insulated top section accepts a wide variety of attachments
- This allows lineman to disconnect switches and replace cutout tubes
- Also allows lineman to remove pole covers, prune trees, plus other overhead tasks
- Sticks retract to approximately 5 ft. for easy truck transport (even in most cab sections)
- Heavy-duty, spring-loaded plastic buttons keep extended tool sections locked in place
- As each section extends and slightly twists, buttons also pop securely into place

Specifications

EU RoHS Indicator	No
Buy America(n) Qualified	Contact Manufacturer

Dimensions

WeightMetric	5.4 kg
--------------	--------

WidthMetric	140 mm
Length - Retracted Metric	1.8 m
Length - Retracted	6.25 ft
HeightMetric	127 mm
Diameter - Rod / Tube	2.5 in
Length Metric	2035 mm
Width	5.5 in
Weight	12.0 lb.
Height	5 in
Length	80.125 in
Lengths - Extended	* 22 ft * 28 ft * 34 ft * 40 ft
Dimensions Metric	2035 mm x 140 mm x 127 mm
Dimensions	80.125 in x 5.5 in x 5 in

General

UPC	096359329152
-----	--------------

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[English\]](#)